

## VD | VDL | VDL EX-Zone 2

Rapid drying with no residues, no danger of incrustation, no oxidation – all under gentle cycle conditions. Safe drying of materials under vacuum always presents a special challenge. You can meet this challenge with confidence, however. Working together with companies in the industry, we have developed a special safety concept that sets new standards for safe interaction, all while maintaining our usual perfect performance and quality.

### BINDER Scientific: Vacuum drying ovens



#### VD series:

The VD series ensures absolute homogenous temperature distribution and incorporates patented expansion rack technology.

[to VD series](#)



#### VDL series:

The VDL series ensures maximum safety when drying organic solvents in accordance with TÜV/GS guidelines. The interior chamber is designed in accordance with the ATEX Directive for Zone 2

[to VDL series](#)



#### VDL EX-Zone 2 series:

The VDL series EX-Zone 2 is designed for operation in explosion hazard areas EX-Zone 2, in full compliance with ATEX requirements.

[to VDL EX-Zone 2 series](#)