



**Bringing Test Innovation to you** 

# Datasheet

This product datasheet has been provided by John Godrich & SJ Electronics in Partnership with BINDER





# Model ED 400 | Drying and heating chambers Classic.Line with natural convection

The strengths of a BINDER ED series drying chamber include routine drying and sterilization tasks up to 300 °C. Thanks to the natural convection, all thermal processes which use this drying chamber are highly efficient. The ED series ensures fast, uniform drying.

#### **BENEFITS**

- Uniform drying conditions thanks to APT.line<sup>™</sup> technology
- · Identical test conditions throughout the chamber interior independent of sample size and quantity
- · Outstanding thermal insulation saves operation costs



Model 400

#### MAIN FEATURES

- Temperature range: room temperature plus 5 °C to 300 °C
- APT.line™ preheating chamber technology
- · Natural convection
- Adjustable exhaust air flap
- · Controller with timer functions
- · 2 chrome-plated racks
- Class 2 independent adjustable temperature safety device (DIN 12880) with visual alarm

#### ORDERING INFORMATION

Interior volume [cu.ft.]	Voltage	Option model	Version	ArtNo.
Model ED 400				
14.1	400 V 3 ph 50/60 Hz	with RS 422	ED400-400V-I	9010-0075
	208 V 3 ph 60 Hz	with RS 422	ED400UL-208V-I	9010-0168



#### **TECHNICAL DATA**

Description	ED400-400V-I <sup>1</sup>	ED400UL-208V-I <sup>1</sup>
Article Number	9010-0075	9010-0168
Performance Data Temperature		
Temperature range 5 °C above ambient temperature to [°C]	300	300
Temperature variation at 150 °C [± K]	3	3
Temperature fluctuation at 150 °C [± K]	0.5	0.5
Heating-up time to 150 °C [min]	71	71
Recovery time after 30 seconds door open at 150 °C [min]	31	31
Air change data		
Air change (approx.) at 150 °C [x/h]	10	10
Electrical data		
Rated Voltage [V]	400	208
Power frequency [Hz]	50/60	60
Nominal power [kW]	3.4	3.4
Unit fuse [A]	3 x 16	3 x 16
Phase (Nominal voltage) [ph]	3	3
Outer dimensions		
Width net [mm]	1235	1235
Height net [mm]	1025	1025
Depth net [mm]	765	765
Wall clearance back [mm]	160	160
Wall clearance sidewise [mm]	100	100
Doors		
Unit doors	2	2
Internal Dimensions		
Width [mm]	1000	1000
Height [mm]	800	800
Depth [mm]	520	520
Measures		
Interior volume [L]	400	400
Net weight of the unit (empty) [kg]	125	125
permitted load [kg]	90	90
Load per rack [kg]	35	35
Environment-specific data		
Energy consumption at 150 °C [Wh/h]	672	672
Fixtures		
Number of shelves (std./max.)	2/10	2/10

<sup>1</sup> All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10%. The temperature data is determined in accordance to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.



## **OPTIONS AND ACCESSORIES**

Designation	Description	*	ArtNo.
	back		<u> </u>
	10 mm	01	8012-1282
	30 mm	01	8012-0540
	50 mm	01	8012-0546
	left		
	10 mm	01	8012-1275
	30 mm	01	8012-0537
	50 mm	01	8012-0542
	100 mm	01, 11	8012-0722
access port with silicone lug	right		
iag	10 mm	01	8012-1268
	30 mm	01	8012-0536
	50 mm	01	8012-0541
	100 mm	01, 11	8012-0721
	top		
	10 mm	01	8012-1262
	30 mm	01	8012-0539
	50 mm	01	8012-0545
	100 mm	01, 10	8012-0547
	Switchable acoustic alarm, with adjustable limit value on the independent temperature safety device		
larm function for verheating	120 V, 208 V option model	_	8012-1303
rverneating	230 V, 400 V option model	_	8012-1299
Analog output, 4 – 20 nA	for temperature values (output not adjustable)	-	8012-0430
Calibration certificate, expanded	for temperature; for extending the measurement in center of chamber to include another test temperature	-	8012-1115
	for temperature, measurement in center of chamber at specified temperature	-	8012-1134
Calibration certificate,	temperature measurement incl. certificate and 27 measuring points at specified temperature	-	8012-1593
emperature	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	-	8012-1572
	temperature measurement incl. certificate, 9 measuring points at specified temperature	-	8012-1551
Cart	Cart – stable cart, casters with locking brakes, dimensions: W 1,300 x D 800 x H 780 mm	-	9051-0019
Class 3.1 independent emperature safety levice	with visual alarm (DIN 12880)	04, 12	8012-0032
Data Logger Kit	T 350: For continuous temperature logging from 0 °C to 350 °C; kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit	19	8012-0714
Data Logger Software	LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable)	19	8012-0821
Door gasket	made of FKM, silicone-free	03	8012-0497
Ooor lock	lockable door handle	_	8012-1253
nner chamber, einforced	including 2 reinforced racks (max. total load 250 kg, max. load per rack 70 kg)	-	8012-1730
	with lid made from 18/8 stainless steel, stackable, dimensions: 230 x 133 x 45 mm		
	small	-	4022-0123
nstrument tray	with lid made from 18/8 stainless steel, stackable, dimensions: 315 x 215 x 60 mm		
	large		4022-0124

<sup>\*</sup> Notes > See last page



Designation	Description	*	ArtNo.
	RS 422 cable set and RS 232 / RS 422 interface converter for connection to 10-way plug distributor or for connection to a unit		
Interface converter	120 V, 60 Hz option model	-	8012-0557
	230 V, 50/60 Hz option model	-	8012-0556
	RS 422 cable set and RS 422 / Ethernet interface converter for connection to 10-way plug distributor or for connection to a unit		
	120 V, 60 Hz option model	-	8012-0405
	230 V, 50/60 Hz option model	-	8012-0380
Interface converter, USB / RS422	RS 422 cable set and RS 422 / USB interface converter for connection to 10-way plug distributor or for connection to a unit (USB-powered converter)	-	8012-0665
Measurement of air exchange rate	in accordance with ASTM D5374, definition and protocol according to ambient temperature	-	8012-0195
pH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-0016
Pt 100 temperature sensor	additional flexible Pt 100, interior, with external connection incl. LEMO connector (3-pin)	-	8012-1173
Rack	chrome plated	-	6004-0005
	stainless steel	-	6004-0011
RS 422 interface	modular plug distributor for 10 RS 422 interfaces	-	8012-0295
RS 422 interface, cable (15 m)	RS 422 connection cable (15 m) between plug distributor and RS 422 interface	-	5023-0036
RS 422 interface, cable (50 m)	RS 422 extension cable (50 m) between interface converter and unit or RS 232 / RS 422 plug distributor	-	5023-0117
Shelf, perforated	stainless steel	-	6004-0032
	APT-COM™ communications software		
	version 2 to 3, GLP edition	19	9053-0016
	version 3, BASIC edition	19	9053-0014
Software	version 3, GLP edition	19	9053-0015
	version 3, STANDARD edition	19	9053-0013
	APT-COM™ communications software, price: for free		
	version 3, GLP DEMO Edition	19	9053-0008
	viewing window in each door, 470 x 290 mm, and 30 W interior lighting		
Viewing window and interior lighting	208 V option model	-	8012-0271
interior lighting	400 V option model	_	8012-0269

<sup>\*</sup> Notes > See last page

## **SERVICES**

Designation	Description	*	ArtNo.
Installation services			
Data Logger Kit installation service	unit function instructions for operation and programming of the controller	18	DL100400
Installation	and set up of unit at operating location, connect to existing connections	13, 18	DL100100
Preventive maintenance			
Preventive maintenance	Execution of equipment inspection according to maintenance plan	14, 18	DL200200
Calibration services			
Data Logger Kit calibration service	including certificate, one measuring point in center of chamber at specified temperature	14, 16, 17, 18	DL300101
Measurement of air exchange rate	including certificate (in accordance with ASTM D5374)	14, 16, 17, 18	DL330000
Temperature measurement 18 measuring points	including certificate, 18 measuring points at specified temperature	14, 16, 17, 18	DL300118
Temperature measurement 27 measuring points	including certificate, 27 measuring points at specified temperature	14, 16, 17, 18	DL300127
Temperature measurement 9 measuring points	including certificate, 9 measuring points at specified temperature	14, 16, 17, 18	DL300109

<sup>\*</sup> Notes > See last page



Designation	Description	*	ArtNo.
Validation services			
Data Logger Kit validation service	in accordance with qualification folder	15, 18, 20	DL400100
Execution of IQ/OQ/PQ	in accordance with customer's requirement, price: on request	15, 18	DL440500
Qualification folder IQ/OQ	supporting documents for validation performed by customer, consisting of: IQ/OQ checklists, unit schematics, QM certificate in accordance with ISO 9001	15, 18, 20	8012-0761
Qualification folder IQ/OQ/PQ	supporting documents for validation performed by customer, in accordance with customer's requirement, extension of Qualification folder IQ/OQ by chapter PQ	15, 18	8012-0942
Warranty service			
Extension of the warranty from 2 to 3 years	beginning with the date of delivery, wearing parts are not included	_	DL002041
Extension of the warranty from 2 to 5 years	beginning with the date of delivery, wearing parts are not included	-	DL002042

<sup>\*</sup> Notes > See last page



#### **NOTES**

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. 01 02
- UL mark is not granted when this option is used. Heat resistant only to max. 200 °C.
- 03
- Only available on units rated for 230 V.
- Heating-up time may increase as a result of the lower heat conductivity.
- The additional heat input may affect the temperature behavior.
- Not in conjunction with the optional access port, door with window and interior lighting. 09
- Not available on 23-liter units.
- Not available on 23- or 53-liter units.
- 10 11 12 Only available on units rated for 230 V or 400 V.
- Installation and connections take place at unit location; transport within the company only upon consultation.
- We recommend a BINDER service contract (see the chapter on BINDER Service) to cover unit inspections, calibrations and validations
- OQ according to Yellow Paper = completed factory validation documentation of all OQ checklists.
- Sensor calibration is performed in an accredited calibration laboratory.
- 17
- Calibration is performed in an accordance cannot about activity.

  Calibration is performed according to the BINDER factory standard.

  Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).
- For additional accessories, refer to the Process documentation chapter.
- When ordering IQ/OQ qualification folders and associated IQ/OQ execution on one order, we offer a 15 % discount for both items.
  - When ordering IQ/OQ/PQ qualification folders and associated IQ/OQ/PQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ/PQ folder.





**Bringing Test Innovation to you** 

# Datasheet

This product datasheet has been provided by John Godrich & SJ Electronics in Partnership with BINDER

