

Datasheet

This product datasheet has been provided by John Godrich & SJ Electronics in Partnership with BINDER



Best conditions for your success

Model FD 56 | Drying and heating chambers Avantgarde.Line with forced convection

A BINDER FD series Avantgarde.Line heating oven is always used when fast drying and sterilization is required. Thanks to its fully homogeneous temperature distribution, quick dynamics and powerful fan, this heating oven saves valuable time.

BENEFITS

- Best energy efficiency on the market
- Excellent temporal and spatial temperature accuracy
- USB connection for recording data
- Temperature range up to 300 °C



Model 56



Model 56

MAIN FEATURES

- Temperature range: ambient temperature plus 10 °C to 300 °C
- Up to 30% lower energy consumption compared to conventional units on the market
- High temperature accuracy thanks to APT.line™ technology
- Forced convection
- Controller with LCD display
- Electromechanical control of the exhaust air flap
- 2 chrome-plated racks
- Stackable
- Class 2 integrated independent adjustable temperature safety device (DIN 12880) with visual alarm
- Ergonomic handle design
- USB port for recording data

ORDERING INFORMATION

| Interior volume [cu.ft.] | Voltage | Option model | Version | Art.-No. |
|--------------------------|---------------------|--------------|--------------|-----------|
| Model FD 56 | | | | |
| 2.1 | 230 V 1 ph 50/60 Hz | Standard | FD056-230V | 9010-0303 |
| | 120 V 1 ph 60 Hz | Standard | FD056UL-120V | 9010-0304 |

TECHNICAL DATA

| Description | FD056-230V ¹ | FD056UL-120V ¹ |
|---|-------------------------|---------------------------|
| Article Number | 9010-0303 | 9010-0304 |
| Performance Data Temperature | | |
| Temperature range 10 °C above ambient temperature to [°C] | 300 | 300 |
| Temperature variation at 150 °C [± K] | 1.7 | 1.7 |
| Temperature fluctuation at 150 °C [± K] | 0.3 | 0.3 |
| Heating-up time to 150 °C [min] | 15 | 15 |
| Recovery time after 30 seconds door open at 150 °C [min] | 4 | 4 |
| Electrical data | | |
| Rated Voltage [V] | 230 | 120 |
| Power frequency [Hz] | 50/60 | 60 |
| Nominal power [kW] | 1.1 | 1.2 |
| Unit fuse [A] | 6.3 | 12.5 |
| Phase (Nominal voltage) [ph] | 1 | 1 |
| Outer dimensions | | |
| Width net [mm] | 560 | 560 |
| Height net [mm] | 625 | 625 |
| Depth net [mm] | 565 | 565 |
| Wall clearance back [mm] | 160 | 160 |
| Wall clearance sidewise [mm] | 100 | 100 |
| Doors | | |
| Unit doors | 1 | 1 |
| Internal Dimensions | | |
| Width [mm] | 400 | 400 |
| Height [mm] | 440 | 440 |
| Depth [mm] | 345 | 345 |
| Measures | | |
| Interior volume [L] | 60 | 60 |
| Net weight of the unit (empty) [kg] | 39 | 39 |
| permitted load [kg] | 70 | 70 |
| Load per rack [kg] | 30 | 30 |
| Environment-specific data | | |
| Energy consumption at 150 °C [Wh/h] | 290 | 290 |
| Sound-pressure level [dB(A)] | 43 | 43 |
| Fixtures | | |
| Number of shelves (std./max.) | 2/4 | 2/4 |

¹ All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.

OPTIONS AND ACCESSORIES

| Designation | Description | * | Art.-No. |
|---|--|-----------|-----------|
| Access port with silicone plug | left | | |
| | 10 mm | 01 | 8012-1276 |
| | 30 mm | 01 | 8012-1016 |
| | 50 mm | 01 | 8012-1020 |
| | right | | |
| | 10 mm | 01 | 8012-1269 |
| | 30 mm | 01 | 8012-1015 |
| | 50 mm | 01 | 8012-1019 |
| | top | | |
| | 10 mm | 01 | 8012-1263 |
| | 30 mm | 01 | 8012-1364 |
| | 50 mm | 01 | 8012-1380 |
| 100 mm | 01, 10 | 8012-1671 | |
| Analog output, 4 – 20 mA | for temperature values (output not adjustable) | 02 | 8012-1624 |
| Calibration certificate, expanded | for temperature; for extending the measurement in center of chamber to include another test temperature | – | 8012-1116 |
| Calibration certificate, temperature | for temperature, measurement in center of chamber at specified temperature | – | 8012-1135 |
| | temperature measurement incl. certificate and 27 measuring points at specified temperature | – | 8012-1594 |
| | temperature measurement incl. certificate, 15- 18 measuring points at specified temperature | – | 8012-1573 |
| | temperature measurement incl. certificate, 9 measuring points at specified temperature | – | 8012-1552 |
| Cart | Cart – stable cart, casters with locking brakes, dimensions: W 1,000 x D 800 x H 780 mm | – | 9051-0018 |
| Class 3.1 independent temperature safety device | with visual alarm (DIN 12880) | 04, 12 | 8012-1643 |
| Clock | battery-backed | – | 8012-1641 |
| Data Logger Kit | T 350: For continuous temperature logging from 0 °C to 350 °C; kit includes 1 data logger, Pt 100 sensor with 2 m extension cable and 1 magnetic fixture for mounting to the BINDER unit | 19 | 8012-0714 |
| Data Logger Software | LOG ANALYZE software kit, configuration and evaluation software for all BINDER Data Logger Kits (incl. USB data cable) | 19 | 8012-0821 |
| Door gasket | made of FKM, silicone-free | 03 | 8012-1648 |
| Door lock | lockable door handle | – | 8012-1665 |
| Ethernet interface | for communication software | – | 8012-0988 |
| Gas-tight option model | Incl. additional measures for the greatest possible impermeability to gas; not in conjunction with access port or interior lighting option | 09 | 8012-1683 |
| Heating output, reinforced | For faster heating up time and improved recovery time; max. 300 °C; not in conjunction with load management option | | |
| | 230 V option model | – | 8012-1056 |
| HEPA air filter | On fresh air supply for unit; filter classification H14 (acc. to. EN 1822-1:2009, > 99.995% at 0.3 µm) | – | 8012-1050 |
| Inert gas connection | With gas inlet and outlet, Ø 10 mm, incl. additional measures for the greatest possible impermeability to gas; not in conjunction with access port or interior lighting option | – | 8012-1689 |
| Inner chamber, reinforced | including 2 reinforced racks (max. total load 250 kg, max. load per rack 70 kg) | – | 8012-1053 |
| Instrument tray | with lid made from 18/8 stainless steel, stackable, dimensions: 230 x 133 x 45 mm | | |
| | small | – | 4022-0123 |
| | with lid made from 18/8 stainless steel, stackable, dimensions: 315 x 215 x 60 mm | | |
| | large | – | 4022-0124 |
| Interior lighting | with 15 W light bulb | | |
| | 120 V option model | – | 8012-1632 |
| | 230 V option model | – | 8012-1628 |
| Measurement of air exchange rate | in accordance with ASTM D5374, definition and protocol according to ambient temperature | – | 8012-1195 |
| Overheating alarm | audible, can be switched off, adjustable limit on the independent temperature safety device | – | 8012-1636 |

* Notes › See last page

| Designation | Description | * | Art.-No. |
|--------------------------------------|--|----|-----------|
| pH-neutral detergent | concentrated, for gentle remove of residual contaminants; 1 kg | - | 1002-0016 |
| Pt 100 temperature sensor | additional flexible Pt 100, interior, for displaying the temperature on the unit display | - | 8012-1620 |
| Rack | chrome plated | - | 6004-0166 |
| | stainless steel | - | 6004-0150 |
| Rack, heavy load | Stainless steel (1.4301/AISI 304), max. load per rack 50 kg, max. total load 70 kg | - | 6004-0198 |
| Rubber pads | set of 4 anti-slip feet, for safe stacking of unit | 10 | 8012-0001 |
| Shelf, perforated | stainless steel | - | 6004-0182 |
| Software | APT-COM™ communications software version 2 to 3, GLP edition | 19 | 9053-0016 |
| | version 3, BASIC edition | 19 | 9053-0014 |
| | version 3, GLP edition | 19 | 9053-0015 |
| | version 3, STANDARD edition | 19 | 9053-0013 |
| | APT-COM™ communications software, price: for free version 3, GLP DEMO Edition | 19 | 9053-0008 |
| Viewing window and interior lighting | viewing window (triple insulating glass) in door, 240 x 240 mm, and 15 W interior | | |
| | 120 V option model | - | 8012-1702 |
| | 230 V option model | - | 8012-1700 |

* Notes › See last page


SERVICES

| Designation | Description | * | Art.-No. |
|---|---|-------------------|-----------|
| Installation services | | | |
| Data Logger Kit installation service | unit function instructions for operation and programming of the controller | 18 | DL100400 |
| Installation | and set up of unit at operating location, connect to existing connections | 13, 18 | DL100100 |
| Preventive maintenance | | | |
| Preventive maintenance | Execution of equipment inspection according to maintenance plan | 14, 18 | DL200200 |
| Calibration services | | | |
| Data Logger Kit calibration service | including certificate, one measuring point in center of chamber at specified temperature | 14, 16, 17, 18 | DL300101 |
| Measurement of air exchange rate | including certificate (in accordance with ASTM D5374) | 14, 16, 17, 18 | DL330000 |
| Temperature measurement 18 measuring points | including certificate, 18 measuring points at specified temperature | 14, 16, 17, 18 | DL300118 |
| Temperature measurement 27 measuring points | including certificate, 27 measuring points at specified temperature | 14, 16, 17, 18 | DL300127 |
| Temperature measurement 9 measuring points | including certificate, 9 measuring points at specified temperature | 14, 16, 17, 18 | DL300109 |
| Validation services | | | |
| Data Logger Kit validation service | in accordance with qualification folder | 15, 18, 20 | DL400100 |
| Execution of IQ/OQ/PQ | in accordance with customer's requirement, price: on request | 15, 18 | DL440500 |
| Qualification folder IQ/OQ | supporting documents for validation performed by customer, consisting of: IQ/OQ checklists, unit schematics, QM certificate in accordance with ISO 9001 | 15, 18, 20 | 8012-0792 |
| Qualification folder IQ/OQ/PQ | supporting documents for validation performed by customer, in accordance with customer's requirement, extension of Qualification folder IQ/OQ by chapter PQ | 15, 18 | 8012-0943 |
| Warranty service | | | |
| Extension of the warranty from 2 to 3 years | beginning with the date of delivery, wearing parts are not included | - | DL003041 |
| Extension of the warranty from 2 to 5 years | beginning with the date of delivery, wearing parts are not included | - | DL003042 |

* Notes › See last page

NOTES

- 01 Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge.
- 02 UL mark is not granted when this option is used.
- 03 Heat resistant only to max. 200 °C.
- 04 Only available on units rated for 230 V.
- 06 Heating-up time may increase as a result of the lower heat conductivity.
- 07 The additional heat input may affect the temperature behavior.
- 09 Not in conjunction with the optional access port, door with window and interior lighting.
- 10 Not available on 23-liter units.
- 11 Not available on 23- or 53-liter units.
- 12 Only available on units rated for 230 V or 400 V.
- 13 Installation and connections take place at unit location; transport within the company only upon consultation.
- 14 We recommend a BINDER service contract (see the chapter on BINDER Service) to cover unit inspections, calibrations and validations.
- 15 OQ according to Yellow Paper = completed factory validation documentation of all OQ checklists.
- 16 Sensor calibration is performed in an accredited calibration laboratory.
- 17 Calibration is performed according to the BINDER factory standard.
- 18 Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).
- 19 For additional accessories, refer to the Process documentation chapter.
- 20 When ordering IQ/OQ qualification folders and associated IQ/OQ execution on one order, we offer a 15 % discount for both items.
When ordering IQ/OQ/PQ qualification folders and associated IQ/OQ/PQ execution on one order, we offer a 15 % discount for the item of the IQ/OQ/PQ folder.



Datasheet

This product datasheet has been provided by John Godrich & SJ Electronics in Partnership with BINDER



Best conditions for your success